

Thread "Go" / "No Go" plug gauge EG 6H mod., Threads: EG-M5



Order data

Order number	486180 EG-M5
GTIN	2050001919175
Item class	48B

Description

Version:

Thread gauge for testing insert threads (EG) of wire thread inserts. The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 – 2299. **"Go" and "No Go" ends on a single handle (DIN 2240, part 1, form R).** "No Go" end marked red.

Application:

For metric ISO-profile insert threads (EG), right-hand DIN 8140-2.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502 und DIN 8140.**

Technical description

Thread	EG M5
Thread pitch	0.8 mm
Thread type	EG-M
Standard	DIN 8140
Type of gauge	"No Go" gauge
Type of gauge	"Go" plug gauge
Calibration	L10
Type of product	Thread Go / NoGo plug gauge

Services

DAkKS calibration "Go" / "No Go" thread plug gauge
maximum Ø 90 mm

028590 90

CalibrationGo / No Go thread plug gauge maximum Ø 20
mm

028550 20