

## Thread "Go" / "No Go" plug gauge EG 6H mod., Threads: EG-M10



### Order data

|              |               |
|--------------|---------------|
| Order number | 486180 EG-M10 |
| GTIN         | 2050001919205 |
| Item class   | 48B           |

### Description

#### Version:

Thread gauge for testing insert threads (EG) of wire thread inserts. The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 – 2299. **"Go" and "No Go" ends on a single handle (DIN 2240, part 1, form R).** "No Go" end marked red.

#### Application:

For metric ISO-profile insert threads (EG), right-hand DIN 8140-2.

#### Standard:

Toleranzen und Abmaße nach **DIN ISO 1502 und DIN 8140.**

### Technical description

|                 |                             |
|-----------------|-----------------------------|
| Thread pitch    | 1.5 mm                      |
| Thread          | EG M10                      |
| Thread type     | EG-M                        |
| Standard        | DIN 8140                    |
| Type of gauge   | "No Go" gauge               |
| Type of gauge   | "Go" plug gauge             |
| Calibration     | L10                         |
| Type of product | Thread Go / NoGo plug gauge |

### Services

DAkKS calibration "Go" / "No Go" thread plug gauge  
maximum  $\varnothing$  90 mm

028590 90

CalibrationGo / No Go thread plug gauge maximum  $\varnothing$  20  
mm

028550 20