



## Double-ended ring spanner, deeply cranked, chrome-plated, Width across flats: 22X24mm



### Order data

Order number	615950 22X24
GTIN	4045197161024
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

#### Standard:

**DIN 838 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Width across flats 1	22 mm
Width across flats 2	24 mm
maximum ring $\varnothing D_1$ max	34 mm
Spanner length L	325 mm
maximum ring $\varnothing D_2$ max	37 mm
Width across flats	metric
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

