



## Double-ended ring spanner, straight, phosphated, Width across flats: 19X22 mm



### Order data

Order number	617900 19X22
GTIN	4045197385765
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

**HOLEX** – With oval shaft.

#### Standard:

**DIN 837 B / ISO 3318**

#### Material:

**HOLEX** – Chrome vanadium steel, phosphated.

Spanner length L: 204 mm

maximum ring  $\varnothing D_1$  max: 29 mm

maximum ring  $\varnothing D_2$  max: 32.4 mm

maximum ring height  $h_{1\max}$ : 10.8 mm

### Technical description

Width across flats 1	19 mm
Width across flats 2	22 mm
maximum ring $\varnothing D_1$ max	29 mm
Spanner length L	204 mm
maximum ring height $h_{1\max}$	10.8 mm
maximum ring $\varnothing D_2$ max	32.4 mm
Width across flats	metric
Ring setting	0 degrees

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner