

ELTEN
Lace-up boots grey VINTAGE Mid ESD, S3, EU shoe size: 44

Order data

Order number	092231 44
GTIN	4030839220580
Item class	09P

Description
Version:

Modern safety shoes in vintage design.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining, BIOACTIVE for a pleasant foot climate.**
- **Padded tongue.**
- **ESD PRO grey full-size insole.**
- **L10 TPU/PU sole, anti-slip.**
- **ESD security.**

Safety shoe with bioactive inner lining. Particularly **gentle to the skin and odour-suppressant**.

Extra laces supplied (grey).

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Supplied with:

With extra laces in grey.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 37 – 48.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Textile

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

against water penetration and water absorption	yes
Material of protective toe-cap	Steel
suitable for orthopaedic insoles	yes
Colour	grey
Standard	Inlay type-tested according to DGUV regulation 191
Energy absorption in the heel area	yes
EU shoe size	44
anti-static	yes
contains no metal or leather	no
Uppers material	Genuine leather
The entire shoe is waterproof	yes
Closure	Laces
Material of outer sole	TPU/PU
Shoe type	Bootlaces
Puncture resistance	Textile
oil- and petrol-resistant sole	yes
Protection class	S3
Material inner lining	breathable textile inner lining
Series	VINTAGE
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots