



## Double-ended ring spanner, straight, phosphated, Width across flats: 14X15 mm



### Order data

Order number	617900 14X15
GTIN	4045197348609
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.

**HOLEX** – With oval shaft.

**Standard:**

**DIN 837 B / ISO 3318**

**Material:**

**HOLEX** – Chrome vanadium steel, phosphated.

Spanner length L: 159 mm

maximum ring  $\varnothing D_1$  max: 21.5 mm

maximum ring  $\varnothing D_2$  max: 23 mm

maximum ring height  $h_{1\max}$ : 7.5 mm

### Technical description

maximum ring $\varnothing D_2$ max	23 mm
Width across flats 2	15 mm
maximum ring $\varnothing D_1$ max	21.5 mm
maximum ring height $h_{1\max}$	7.5 mm
Spanner length L	159 mm
Width across flats 1	14 mm
Width across flats	metric
Ring setting	0 degrees

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner