



Double-ended ring spanner, straight, Width across flats: 30X34mm



Order data

Order number	617600 30X34
GTIN	4018754021437
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

STAHLWILLE – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS-Drive** profile.

Standard:

DIN 837 B / ISO 3318

Material:

STAHLWILLE – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

Technical description

maximum ring $\varnothing D_2$ max	48.5 mm
maximum ring $\varnothing D_1$ max	43 mm
Width across flats 2	34 mm
Width across flats 1	30 mm
Spanner length L	325 mm
maximum ring height $h_{1\max}$	13.8 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated (non-flaking)

Type of product

Spanner