



Double-ended ring spanner, deeply cranked, chrome-plated, Width across flats: 32X36mm



Order data

| | |
|--------------|---------------|
| Order number | 615950 32X36 |
| GTIN | 4045197441799 |
| Item class | 62A |

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

| | |
|------------------------------------|---------------|
| Width across flats 1 | 32 mm |
| maximum ring $\varnothing D_1$ max | 48 mm |
| maximum ring $\varnothing D_2$ max | 52 mm |
| Width across flats 2 | 36 mm |
| Spanner length L | 410 mm |
| Width across flats | metric |
| Surface | chrome plated |
| Product name attribute | chrome-plated |
| Type of product | Spanner |

