



## Double-ended ring spanner, straight, Width across flats: 18X19mm



### Order data

Order number	617600 18X19
GTIN	4018754021345
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

**STAHLWILLE** – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS-Drive** profile.

#### Standard:

**DIN 837 B / ISO 3318**

#### Material:

**STAHLWILLE** – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

### Technical description

Spanner length L	185 mm
maximum ring $\varnothing D_2$ max	27.6 mm
Width across flats 2	19 mm
Width across flats 1	18 mm
maximum ring $\varnothing D_1$ max	26.5 mm
maximum ring height $h_{1\max}$	9 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated (non-flaking)

Type of product

Spanner