



## Double-ended ring spanner, straight, phosphated, Width across flats: 17X19 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 617900 17X19  |
| GTIN         | 4045197385734 |
| Item class   | 62A           |

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

**HOLEX** – With oval shaft.

#### Standard:

**DIN 837 B / ISO 3318**

#### Material:

**HOLEX** – Chrome vanadium steel, phosphated.

Spanner length L: 184 mm

maximum ring  $\varnothing D_1$  max: 26.5 mm

maximum ring  $\varnothing D_2$  max: 27.6 mm

maximum ring height  $h_{1\max}$ : 8.8 mm

### Technical description

|                                    |           |
|------------------------------------|-----------|
| Width across flats 1               | 17 mm     |
| maximum ring $\varnothing D_1$ max | 26.5 mm   |
| maximum ring $\varnothing D_2$ max | 27.6 mm   |
| Spanner length L                   | 184 mm    |
| maximum ring height $h_{1\max}$    | 8.8 mm    |
| Width across flats 2               | 19 mm     |
| Width across flats                 | metric    |
| Ring setting                       | 0 degrees |

|                        |                       |
|------------------------|-----------------------|
| Manufacturing process  | drop forged           |
| Material               | Chrome vanadium steel |
| Surface                | phosphated            |
| Product name attribute | phosphated            |
| Type of product        | Spanner               |