



Multi-standard dungarees Multiseven, yellow / cornflower blue, Clothing size DE: 90



Order data

Order number	091785 90
GTIN	4046181590615
Item class	09S

Description

Version:

Dungarees with stretch braces for high wearer comfort, ideal for welding work.

- **Bib patch pocket with flap and hook and loop fastener.**
- **Waist highly adjustable.**
- **Two side access pockets.**
- **Cargo pocket with a mobile phone patch pocket on it.**
- **Back patch pocket with flap and hook and loop fastener.**

Standard:

EN ISO 20471, Klasse 1; EN 1149-3-5; EN 61482-1-2, Klasse 1; EN ISO 11611, Klasse 1 A1; EN ISO 11612 A1, B1, C1, E2, F1; EN ISO 13034 Typ 6;

Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Fabric composition: 43% cotton

Fabric composition: 2% special fibres

Fabric composition: 55% modacrylic

Material weight/fabric density: 350 g/m²

Washing: 60 °C coloureds

Clothing to: Protection to DIN EN ISO 11612 against flames and heat

Technical description

Clothing size DE	90
Gender	Gentlemen's
Fabric composition	43% cotton
Fabric composition	2% special fibres
Fabric composition	55% modacrylic
Material weight/fabric density	350 g/m ²
Washing	60 °C coloureds
Bleaching	do not bleach
Dry-cleaning	gentle cleaning with perchlorethylene
Drying	gentle tumble drying (low temperature)
Ironing	moderately hot, up to maximum 150 °C
Clothing to	Protection to DIN EN ISO 11612 against flames and heat
Clothing to	Anti-static characteristics to DIN EN ISO 1149
Clothing to	Protection to DIN EN ISO 11611 when welding
Colour	yellow / cornflower blue
Norm	EN 61482-1-2
Norm	EN 13034-6
Norm	EN ISO 20471