



Multi-standard dungarees Multiseven, yellow / cornflower blue, Clothing size DE: 94



Order data

| | |
|--------------|---------------|
| Order number | 091785 94 |
| GTIN | 4046181590622 |
| Item class | 09S |

Description

Version:

Dungarees with stretch braces for high wearer comfort, ideal for welding work.

- **Bib patch pocket with flap and hook and loop fastener.**
- **Waist highly adjustable.**
- **Two side access pockets.**
- **Cargo pocket with a mobile phone patch pocket on it.**
- **Back patch pocket with flap and hook and loop fastener.**

Standard:

EN ISO 20471, Klasse 1; EN 1149-3-5; EN 61482-1-2, Klasse 1; EN ISO 11611, Klasse 1 A1; EN ISO 11612 A1, B1, C1, E2, F1; EN ISO 13034 Typ 6;

Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Fabric composition: 43% cotton

Fabric composition: 2% special fibres

Fabric composition: 55% modacrylic

Material weight/fabric density: 350 g/m²

Washing: 60 °C coloureds

Clothing to: Protection to DIN EN ISO 11612 against flames and heat

Technical description

| | |
|--------------------------------|-----------------------------------------------------------|
| Clothing size DE | 94 |
| Gender | Gentlemen's |
| Fabric composition | 43% cotton |
| Fabric composition | 2% special fibres |
| Fabric composition | 55% modacrylic |
| Material weight/fabric density | 350 g/m ² |
| Washing | 60 °C coloureds |
| Bleaching | do not bleach |
| Dry-cleaning | gentle cleaning with perchlorethylene |
| Drying | gentle tumble drying (low temperature) |
| Ironing | moderately hot, up to maximum 150 °C |
| Clothing to | Protection to DIN EN ISO 11612 against flames and heat |
| Clothing to | Anti-static characteristics to DIN EN ISO 1149 |
| Clothing to | Protection to DIN EN ISO 11611 when welding |
| Colour | yellow / cornflower blue |
| Norm | EN 61482-1-2 |
| Norm | EN 13034-6 |
| Norm | EN ISO 20471 |