



Double-ended ring spanner, straight, Width across flats: 18X21 mm



Order data

Order number	617600 18X21
GTIN	4018754021352
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

STAHLWILLE – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS-Drive** profile.

Standard:

DIN 837 B / ISO 3318

Material:

STAHLWILLE – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

Technical description

maximum ring height $h_{1 \max}$	9.8 mm
maximum ring $\varnothing D_2 \max$	30.5 mm
Width across flats 2	21 mm
Spanner length L	210 mm
Width across flats 1	18 mm
maximum ring $\varnothing D_1 \max$	26.5 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated (non-flaking)

Type of product

Spanner