



## Double-ended ring spanner, straight, phosphated, Width across flats: 18X19 mm



### Order data

Order number	617900 18X19
GTIN	4045197385741
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

**HOLEX** – With oval shaft.

#### Standard:

**DIN 837 B / ISO 3318**

#### Material:

**HOLEX** – Chrome vanadium steel, phosphated.

Spanner length L: 184 mm

maximum ring  $\varnothing D_1$  max: 26.5 mm

maximum ring  $\varnothing D_2$  max: 27.6 mm

maximum ring height  $h_{1\max}$ : 9 mm

### Technical description

Spanner length L	184 mm
Width across flats 1	18 mm
maximum ring height $h_{1\max}$	9 mm
maximum ring $\varnothing D_1$ max	26.5 mm
Width across flats 2	19 mm
maximum ring $\varnothing D_2$ max	27.6 mm
Width across flats	metric
Ring setting	0 degrees

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner