



Double-ended ring spanner, straight, chrome-plated, Width across flats: 16X17mm



Order data

Order number	617950 16X17
GTIN	4045197441898
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.

HOLEX – With oval shaft.

Standard:

DIN 837 B / ISO 3318

Material:

HOLEX – Chrome vanadium steel, chrome-plated.

Technical description

Width across flats 2	17 mm
maximum ring $\varnothing D_2$ max	25.5 mm
Spanner length L	169 mm
Width across flats 1	16 mm
maximum ring height $h_{1\max}$	8 mm
maximum ring $\varnothing D_1$ max	24.5 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome plated

Product name attribute	chrome-plated
Type of product	Spanner