



Double-ended ring spanner set, straight, phosphated, Number of keys: 8



Order data

Order number	617910 8
GTIN	4045197385802
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.

HOLEX – With oval shaft.

Standard:

DIN 837 B / ISO 3318

Material:

HOLEX – Chrome vanadium steel, phosphated.

Content:

1 each double ended ring spanner No. 617600 / 617900 / 617950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22

Supplied with:

1 each double ended ring spanner No. 617600 / 617900 / 617950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22

Technical description

Number of keys	8
Width across flats	metric
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

Accessories

Double-ended ring spanner, straight Width across flats 18X21 mm	617900 18X21
Double-ended ring spanner, straight Width across flats 12X13 mm	617900 12X13
Double-ended ring spanner, straight Width across flats 19X22 mm	617900 19X22
Double-ended ring spanner, straight Width across flats 14X15 mm	617900 14X15
Double-ended ring spanner, straight Width across flats 6X7 mm	617900 6X7
Double-ended ring spanner, straight Width across flats 16X17 mm	617900 16X17
Double-ended ring spanner, straight Width across flats 10X11 mm	617900 10X11
Double-ended ring spanner, straight Width across flats 8X9 mm	617900 8X9