



Double-ended ring spanner, straight, Width across flats: 19X22mm



Order data

Order number	617600 19X22
GTIN	4018754021369
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

STAHLWILLE – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS-Drive** profile.

Standard:

DIN 837 B / ISO 3318

Material:

STAHLWILLE – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

Technical description

Width across flats 2	22 mm
maximum ring height $h_{1\ max}$	10.8 mm
Width across flats 1	19 mm
maximum ring $\varnothing D_2\ max$	32.4 mm
maximum ring $\varnothing D_1\ max$	29 mm
Spanner length L	210 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated (non-flaking)

Type of product

Spanner