



Rigid endoscope, Ø 4 mm, Working length (without lens): 145mm



Order data

| | |
|--------------|------------|
| Order number | 492734 145 |
| GTIN | |
| Item class | 49C |

Description

Version:

The sturdy stainless steel tube and high-quality optics are specially well suited for rough industrial environments. Easy to connect to the required light source for the standard fibre optic cable connection (ACMI). Focusing works via a twist ring on the eyepiece. Easy focusing in the foreground and background without moving the endoscope. Bright, colour-corrected bar optics.

Suitable for:

FlexiVision 100 with HD camera head No. 492866.

Supplied with:

With interchangeable lens with direction of view 0°.

Optional extras:

LED light sources No. 492846 and No. 462860.

Note:

Using slip-on mirror sleeves the direction of view can be changed to 70° or 90°. When mirror sleeves are used the working diameter increases according to the mirror sleeve. Mirror sleeves and exchangeable lenses available on request.

Technical description

| | |
|-------------------------------|-----------|
| Direction of view | 0° |
| Image aperture angle | 35° |
| Working length (without lens) | 145 mm |
| Probe Ø | 4 mm |
| Product name attribute | Ø 4 mm |
| Type of product | Endoscope |

Accessories

| | |
|---|---------------|
| Cold light source LED Type FX4000 | 492860 FX4000 |
| LED light source | 492846 |
| Flexible fibre optic cable Working length 1800 mm | 492850 1800 |
| Endoscopy video camera CCD | 492837 |