



## Rigid endoscope, Ø 5.5 mm, Working length (without lens): 355mm



### Order data

Order number	492736 355
GTIN	2050001956927
Item class	49C

### Description

#### Version:

The sturdy stainless steel tube and high-quality optics are specially well suited for rough industrial environments. Easy to connect to the required light source for the standard fibre optic cable connection (ACMI). Focusing works via a twist ring on the eyepiece. Easy focusing in the foreground and background without moving the endoscope. Bright, colour-corrected bar optics.

#### Suitable for :

FlexiVision 100 with HD camera head No. 492866.

#### Supplied with:

With interchangeable lens with direction of view 0°.

#### Optional extras:

LED light sources No. 492846 and No. 462860.

#### Note:

Using slip-on mirror sleeves the direction of view can be changed to 70° or 90°. When mirror sleeves are used the working diameter increases according to the mirror sleeve. Mirror sleeves and exchangeable lenses available on request.

Direction of view: 0°

Image aperture angle: 40°

### Technical description

Direction of view	0°
Image aperture angle	40°
Working length (without lens)	355 mm
Probe Ø	5.5 mm
Product name attribute	Ø 5.5 mm

Type of product

Endoscope

---

**Accessories**

Endoscopy video camera CCD

492837

Flexible fibre optic cable Working length 1800 mm

492850 1800

LED light source

492846

Cold light source LED Type FX4000

492860 FX4000