



## Double-ended ring spanner, straight, phosphated, Width across flats: 18X21 mm



### Order data

Order number	617900 18X21
GTIN	4045197385758
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

**HOLEX** – With oval shaft.

#### Standard:

**DIN 837 B / ISO 3318**

#### Material:

**HOLEX** – Chrome vanadium steel, phosphated.

Spanner length L: 194 mm

maximum ring  $\varnothing D_1$  max: 26.5 mm

maximum ring  $\varnothing D_2$  max: 30.5 mm

maximum ring height  $h_{1\max}$ : 9.8 mm

### Technical description

Width across flats 2	21 mm
Spanner length L	194 mm
maximum ring $\varnothing D_2$ max	30.5 mm
maximum ring height $h_{1\max}$	9.8 mm
Width across flats 1	18 mm
maximum ring $\varnothing D_1$ max	26.5 mm
Width across flats	metric
Ring setting	0 degrees

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner