



## Rigid micro-endoscope, Ø 2.7 mm, Working length (without lens) (without lens): 185mm



### Order data

Order number	492746 185
GTIN	
Item class	49C

### Description

#### Version:

Small diameter for measuring small components.

The sturdy stainless steel tube and high-quality optics are specially well suited for rough industrial environments. Easy to connect to the required light source for the standard fibre optic cable connection (ACMI). Focusing works via a twist ring on the eyepiece. Easy focusing in the foreground and background without moving the endoscope. Bright, colour-corrected bar optics.

#### Suitable for:

FlexiVision 100 with HD camera head No. 492866.

#### Optional extras:

LED light sources No. 492846 and No. 462860.

#### Note:

Using slip-on mirror sleeves the direction of view can be changed to 70° or 90°. When mirror sleeves are used the working diameter increases according to the mirror sleeve. Mirror sleeves and exchangeable lenses available on request.

### Technical description

Direction of view	0°
Image aperture angle	35°
Working length (without lens)	185 mm
Probe Ø	2.7 mm
Product name attribute	Ø 2.7 mm
Type of product	Endoscope

---

## Accessories

Endoscopy video camera CCD	492837
LED light source	492846
Cold light source LED Type FX4000	492860 FX4000
Flexible fibre optic cable Working length 1800 mm	492850 1800