

**Rigid micro-endoscope, Ø 1.8 mm, Working length (without lens): 160mm****Order data**

Order number	492744 160
GTIN	
Item class	49C

**Description****Version:**

The sturdy stainless steel tube and high-quality optics are specially well suited for rough industrial environments. Easy to connect to the required light source for the standard fibre optic cable connection (ACMI). Focusing works via a twist ring on the eyepiece. Easy focusing in the foreground and background without moving the endoscope. Bright, colour-corrected bar optics. Small diameter for measuring small components.

**Suitable for:**

FlexiVision 100 with HD camera head No. 492866.

**Optional extras:**

LED light sources No. 492846 and No. 462860.

**Note:**

Using slip-on mirror sleeves the direction of view can be changed to 70° or 90°. When mirror sleeves are used the working diameter increases according to the mirror sleeve. Mirror sleeves and exchangeable lenses available on request.

**Technical description**

Direction of view	0 °
Image aperture angle	30 °
Working length (without lens)	160 mm
Probe Ø	1.8 mm
Product name attribute	Ø 1.8 mm
Type of product	Endoscope

---

## Accessories

LED light source	492846
Flexible fibre optic cable Working length 1800 mm	492850 1800
Endoscopy video camera CCD	492837
Cold light source LED Type FX4000	492860 FX4000