



## Double-ended ring spanner, straight, chrome-plated, Width across flats: 30X32mm



### Order data

Order number	617950 30X32
GTIN	4045197441973
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

**HOLEX** – With oval shaft.

#### Standard:

**DIN 837 B / ISO 3318**

#### Material:

**HOLEX** – Chrome vanadium steel, chrome-plated.

### Technical description

Width across flats 2	32 mm
Width across flats 1	30 mm
maximum ring $\varnothing D_1$ max	43 mm
Spanner length L	318 mm
maximum ring $\varnothing D_2$ max	48.5 mm
maximum ring height $h_{1\max}$	12.8 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome plated

Product name attribute	chrome-plated
Type of product	Spanner