



## Dungarees Quality Dress, pale grey, Clothing size DE: 46



### Order data

Order number	091132 46
GTIN	4014382988685
Item class	09S

### Description

#### Version:

**Quality Dress** workwear, 100 % cotton fabric. Cotton is especially resistant to chemical and mechanical influences and also to heat. Cotton is a natural product which is comfortable to wear due to its temperature-regulating properties and high absorbency.

**Dungarees** with 6 cm waistband adjustment.

- **Sewn-on raised kidney protection.**
- **Open bib patch pocket with hook and loop sub-division.**
- **Double bib with zip fastener pocket.**
- **Impact resistant and heat-resistant plastic buckle.**

#### Description:

- **Zip fastener in the flies.**
- **Two reinforced front patch pockets.**
- **Thigh pocket.**
- **Mobile phone patch pocket.**
- **Reinforced knee area.**
- **Ruler pocket.**

#### Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

**Available in other colours on request.**

**Dungarees in cornflower blue** under No. 091131.

Fabric composition: 100% cotton

Material weight/fabric density: 285 g/m<sup>2</sup>

Clothing standard: UV standard 801

Washing: 60 °C coloureds

**Technical description**

Trouser leg end form	straight, open
Size FR	40
Number of metre rule pockets	1
Mobile phone pocket	yes
Bib pocket	patch, with hook and loop sub-division
Trouser flies	Zip fastener
Material	Cotton
Plug cap	impact-resistant and heat-resistant plastic buckle
Number of side pockets	2
Side pockets	patch, reinforced
Unisex size	5
reinforced knee area	yes
Clothing size DE	46
Number of knee pockets	2
double bib with zip fastener pocket.	yes
Number of thigh pockets	1
Kidney protection	yes
Size UK	30R
Size US	32/31
Size IT	40
Series	QUALITY DRESS
Special service provision	Textile finishing

Size ES	40
Size NL	46
Gender	Gentlemen's
Fabric composition	100% cotton
Material weight/fabric density	285 g/m <sup>2</sup>
Clothing standard	UV standard 801
Washing	60 °C coloureds
Bleaching	do not bleach
Dry-cleaning	Cleaning with perchlorethylene
Drying	gentle tumble drying (low temperature)
Ironing	moderately hot, up to maximum 150 °C
Colour	pale grey
Type of product	Dungarees