

**LENOX** **Carbide hole saw, Diameter: 32 mm****Order data**

|              |              |
|--------------|--------------|
| Order number | 589060 32    |
| GTIN         | 082472302202 |
| Item class   | 58Z          |

**Description****Version:**

**Carbide-tipped teeth** with long working life.

**Application:**

For cutting **fibre-reinforced plastics (GRP / CRP)**, plasterboard, concrete, sandwich composites, hardwoods. **Vario tooth pitch 3 / 4 tpi**, maximum cutting depth for all sizes **38 mm**. Blows and impacts on carbide cutters can lead to splintering.

**Note:**

Diamond hole saws for cutting glass, tiles, ceramic etc. are available on request.

**Technical description**

|                 |          |
|-----------------|----------|
| Diameter        | 32 mm    |
| Type of product | Hole saw |

**Accessories**

|                                       |             |
|---------------------------------------|-------------|
| Centre drill HSS Type 6KT             | 589430 6KT  |
| Quick-change mounting shank Type 210S | 589314 210S |
| Shank Type 210S                       | 589310 210S |
| Shank Type 210L                       | 589310 210L |
| Centre drill carbide-tipped Type 6KT  | 589432 6KT  |