



Slogging ring spanner, straight, Width across flats: 75mm



Order data

Order number	619000 75
GTIN	4018754023271
Item class	63A

Description

Version:

Drop forged, with short, strong profile shaft and reinforced striking end. Extremely thin ring, exact tolerance jaw widths for working on bolts in very restricted places. The ring is higher than standard nuts, thus jamming is impossible. Stronger than any bolt.

Material:

Chrome alloy steel, painted green.

Technical description

Spanner length L	360 mm
Ring Ø D	103.5 mm
Width across flats	75 mm
Ring thickness h	51 mm
Standard	DIN 7444
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	painted green
Type of product	Spanner

