



## Slogging ring spanner, straight, Width across flats: 80mm



### Order data

Order number	619000 80
GTIN	4018754023295
Item class	63A

### Description

**Version:**

Drop forged, with short, strong profile shaft and reinforced striking end. Extremely thin ring, exact tolerance jaw widths for working on bolts in very restricted places. The ring is higher than standard nuts, thus jamming is impossible. Stronger than any bolt.

**Material:**

Chrome alloy steel, painted green.

### Technical description

Spanner length L	440 mm
Width across flats	80 mm
Ring thickness h	57 mm
Ring $\varnothing$ D	110 mm
Standard	DIN 7444
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	painted green
Type of product	Spanner

