



Slogging ring spanner, straight, Width across flats: 32mm



Order data

Order number	619000 32
GTIN	4018754023141
Item class	63A

Description

Version:

Drop forged, with short, strong profile shaft and reinforced striking end. Extremely thin ring, exact tolerance jaw widths for working on bolts in very restricted places. The ring is higher than standard nuts, thus jamming is impossible. Stronger than any bolt.

Material:

Chrome alloy steel, painted green.

Technical description

Ring thickness h	24 mm
Ring \varnothing D	47 mm
Spanner length L	195 mm
Width across flats	32 mm
Standard	DIN 7444
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	painted green
Type of product	Spanner

