

LENOX **Carbide hole saw, Diameter: 38 mm****Order data**

Order number	589060 38
GTIN	082472302240
Item class	58Z

Description**Version:**

Carbide-tipped teeth with long working life.

Application:

For cutting **fibre-reinforced plastics (GRP / CRP)**, plasterboard, concrete, sandwich composites, hardwoods. **Vario tooth pitch 3 / 4 tpi**, maximum cutting depth for all sizes **38 mm**. Blows and impacts on carbide cutters can lead to splintering.

Note:

Diamond hole saws for cutting glass, tiles, ceramic etc. are available on request.

Technical description

Diameter	38 mm
Type of product	Hole saw

Accessories

Centre drill HSS Type 6KT	589430 6KT
Quick-change mounting shank Type 210S	589314 210S
Centre drill carbide-tipped Type 6KT	589432 6KT
Shank Type 210S	589310 210S
Shank Type 210L	589310 210L