



## Low-profile shoe, black/violet Vitality Plus 439 ESD, S2 XB, EU shoe size: 35



### Order data

Order number	092712 35
GTIN	4044348453896
Item class	09C

### Description

#### Version:

VITALITY PLUS low-profile ladies' safety shoes with **SECURA VARIO Vitality® multi-zone damping** and **STEITZ FLEX-ZONE®** sole tread with flexure zone.

- **Ultra-light functional outer material with breathable textile inserts.**
- **Closed tongue.**
- **Safety reflectors.**
- **ERGO-SOFT ESD comfort footbed inlay.**
- **Real leather inner sole.**
- **TPU-Dynamics sole tread, white.**
- **Protection against electrostatic discharge (ESD).**

Low-profile shoe with closed tongue and real leather upper sole.

- **Aluminium toecap.**
- **TPU-Dynamics sole.**
- **Lightweight sole structure with waisted instep.**

#### Standard:

EN ISO 20345:2011 S2 SRC

#### Note:

EU shoe sizes 36 – 41 held in stock, EU shoe sizes 35 – 42 can be ordered.

electrical insulation: EGB/ESD

Protection class: S2

Puncture resistance: Textile

Norm: Inlay supply design type tested to DGUV regulations 191

## Technical description

EU shoe size	35
Protection class	S2
Puncture resistance	Textile
Norm	Inlay supply design type tested to DGUV regulations 191
Gender	Gentlemen's
electrical insulation	EGB/ESD
Type of product	Safety shoes