

Garant**Hole saw set, Type: 16-76****Order data**

Order number	589710 16-76
GTIN	4045197158772
Item class	51S

Description**Version:**

Bi-metal hole saw set with popular hole saw diameters. HSS Vario tothing for smooth cutting and long service life.

With precision rigid foam inlay for secure retention and easy removal of the hole saws. Stackable modular bar.

Supplied with:

Impact-resistant plastic box with bi-metal hole saws, mounting shafts and centre drills.

Technical description

Hole saw Ø	16; 19; 22; 25; 29; 32; 35; 38; 44; 51; 68; 76 mm
Number of mounting shafts	2
Number of centre drills	5
Number of pieces	19
Type of product	Hole saw

Accessories

Modular box Type 4-2	630310 4-2
Hole saw, bi-metal Diameter 51 mm	589010 51
Hole saw, bi-metal Diameter 29 mm	589010 29
Hole saw, bi-metal Diameter 76 mm	589010 76
Hole saw, bi-metal Diameter 68 mm	589010 68
Hole saw, bi-metal Diameter 25 mm	589010 25
Hole saw, bi-metal Diameter 35 mm	589010 35
Hole saw, bi-metal Diameter 22 mm	589010 22
Hole saw, bi-metal Diameter 38 mm	589010 38
Hole saw, bi-metal Diameter 32 mm	589010 32
Hole saw, bi-metal Diameter 19 mm	589010 19
Hole saw, bi-metal Diameter 16 mm	589010 16
Hole saw, bi-metal Diameter 44 mm	589010 44
Centre drill HSS Type 6KT	589428 6KT
Drive shank Type 210S	589305 210S
Drive shank Type 30	589305 30