



Slogging ring spanner, straight, Width across flats: 85mm



Order data

Order number	619000 85
GTIN	4018754023318
Item class	63A

Description

Version:

Drop forged, with short, strong profile shaft and reinforced striking end. Extremely thin ring, exact tolerance jaw widths for working on bolts in very restricted places. The ring is higher than standard nuts, thus jamming is impossible. Stronger than any bolt.

Material:

Chrome alloy steel, painted green.

Technical description

Width across flats	85 mm
Ring thickness h	57 mm
Spanner length L	440 mm
Ring \varnothing D	117 mm
Standard	DIN 7444
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	painted green
Type of product	Spanner

