



Slogging ring spanner, straight, Width across flats: 36mm



Order data

| | |
|--------------|---------------|
| Order number | 619000 36 |
| GTIN | 4018754023165 |
| Item class | 63A |

Description

Version:

Drop forged, with short, strong profile shaft and reinforced striking end. Extremely thin ring, exact tolerance jaw widths for working on bolts in very restricted places. The ring is higher than standard nuts, thus jamming is impossible. Stronger than any bolt.

Material:

Chrome alloy steel, painted green.

Technical description

| | |
|-----------------------|--------------------|
| Width across flats | 36 mm |
| Ring Ø D | 52.4 mm |
| Spanner length L | 195 mm |
| Ring thickness h | 26 mm |
| Standard | DIN 7444 |
| Manufacturing process | drop forged |
| Material | Chrome alloy steel |
| Surface | painted green |
| Type of product | Spanner |

