



Double-ended ring spanner, straight, chrome-plated, Width across flats: 18X21mm



Order data

Order number	617950 18X21
GTIN	4045197441935
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.

HOLEX – With oval shaft.

Standard:

DIN 837 B / ISO 3318

Material:

HOLEX – Chrome vanadium steel, chrome-plated.

Technical description

maximum ring $\varnothing D_2$ max	30.5 mm
maximum ring height $h_{1\ max}$	9.8 mm
Width across flats 2	21 mm
Width across flats 1	18 mm
Spanner length L	194 mm
maximum ring $\varnothing D_1$ max	26.5 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome plated

Product name attribute	chrome-plated
Type of product	Spanner