

**Garant****Hole saw set, Type: 19-121****Order data**

Order number	589710 19-121
GTIN	4045197672100
Item class	51S

**Description****Version:**

Bi-metal hole saw set with popular hole saw diameters. HSS Vario tothing for smooth cutting and long service life.

With precision rigid foam inlay for secure retention and easy removal of the hole saws. Stackable modular bar.

**Supplied with:**

Impact-resistant plastic box with bi-metal hole saws, mounting shafts and centre drills.

**Technical description**

Number of pieces	23
Number of mounting shafts	2
Hole saw $\varnothing$	19; 22; 25; 29; 35; 38; 44; 51; 57; 68; 76; 83; 92; 95; 105; 121 mm
Number of centre drills	5
Type of product	Hole saw

## Accessories

Hole saw, bi-metal Diameter 57 mm	589010 57
Hole saw, bi-metal Diameter 19 mm	589010 19
Hole saw, bi-metal Diameter 44 mm	589010 44
Hole saw, bi-metal Diameter 92 mm	589010 92
Hole saw, bi-metal Diameter 95 mm	589010 95
Modular box Type 4-2	630310 4-2
Hole saw, bi-metal Diameter 51 mm	589010 51
Hole saw, bi-metal Diameter 121 mm	589010 121
Hole saw, bi-metal Diameter 76 mm	589010 76
Hole saw, bi-metal Diameter 105 mm	589010 105
Hole saw, bi-metal Diameter 22 mm	589010 22
Hole saw, bi-metal Diameter 25 mm	589010 25
Hole saw, bi-metal Diameter 38 mm	589010 38
Hole saw, bi-metal Diameter 29 mm	589010 29
Hole saw, bi-metal Diameter 35 mm	589010 35
Hole saw, bi-metal Diameter 68 mm	589010 68
Hole saw, bi-metal Diameter 83 mm	589010 83
Centre drill HSS Type 6KT	589428 6KT
Drive shank Type 210S	589305 210S
Drive shank Type 30	589305 30