

**Slogging ring spanner, straight, Width across flats: 41 mm****Order data**

Order number	619000 41
GTIN	4018754023172
Item class	63A

Description**Version:**

Drop forged, with short, strong profile shaft and reinforced striking end. Extremely thin ring, exact tolerance jaw widths for working on bolts in very restricted places. The ring is higher than standard nuts, thus jamming is impossible. Stronger than any bolt.

Material:

Chrome alloy steel, painted green.

Technical description

Ring thickness h	29 mm
Spanner length L	200 mm
Width across flats	41 mm
Ring \varnothing D	59 mm
Standard	DIN 7444
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	painted green
Type of product	Spanner

