

Garant GRIDLINE

LED lamp for roller cabinets without support columns, Type: 20**Order data**

Order number	914870 20
GTIN	4045197893734
Item class	9GT

Description**Version:**

Lighting unit complete with lampholder and connecting cable and support arms for mounting on support columns of roller cabinets and mobile workbenches. A carrier arm with break-through for leading the cable through the support columns. Maintenance-free LED technology with long working life. The energy-efficient light source is exceptionally uniform, dazzle-free and flicker-free, with a neutral white light and a light temperature of 4000 K.

This lamp incorporates built-in LED bulbs.

The LED bulbs cannot be exchanged within the lamp.

Suitable for :

Perforated panels No. 914851; 914852 (not suitable for size 222 and size 444).

Supplied with:

LED light including power supply unit, with Wieland plug for connection to cable reels, 2 support arms.

Note:

Also order cable roll-up drum no. 914890 size DE for the power connection.

Power consumption: 20 W

Illumination: 1700 lm

Lamp body length: 625 mm

Lamp body width: 123 mm

Lamp body height: 33 mm

Support arm reach: 350 mm

Technical description

Lamp body width	123 mm
Lamp body length	625 mm
Illumination	1700 lm
Power consumption	20 W
Power supply	Mains-powered
Lamp body height	33 mm
Support arm reach	350 mm
ATEX zone	no
Nominal voltage	250 V
Plug type, input	GST plug-in system
Type of product	Mounted light