

Garant GRIDLINE

LED lamp for ToolTruck without support columns, Type: 20**Order data**

Order number	914872 20
GTIN	4045197893758
Item class	9GT

Description**Version:**

Lighting unit complete with lampholder and connecting cable and support arms for mounting on support columns of roller cabinets and mobile workbenches. A carrier arm with break-through for leading the cable through the support columns. Maintenance-free LED technology with long working life. The energy-efficient light source is exceptionally uniform, dazzle-free and flicker-free, with a neutral white light and a light temperature of 4000 K.

The lamp incorporates built-in LED bulbs. The bulbs cannot be replaced within the lamp.

Suitable for:

Perforated panels No. 914855; 914856 (not suitable for size 222 and size 444).

Supplied with:

LED light including power supply unit, with Wieland plug for connection to cable reels, 2 support arms.

Note:

Also order cable roll-up drum no. 914890 size DE for the power connection.

Technical description

Illumination	2800 lm
Power supply	Mains-powered
Power consumption	35 W
Lamp body width	123 mm

Lamp body height	33 mm
Lamp body length	1030 mm
Support arm reach	350 mm
ATEX zone	no
Series	ToolTruck
Nominal voltage	250 V
Plug type, input	GST plug-in system
Type of product	Mounted light