

**Cordless drill / driver, wireless charging, Manufacturer ID: GSR1860CW****Order data**

Order number	070247 GSR1860CW
GTIN	3165140867269
Item class	03B

Description**Version:**

Bosch cordless drill / driver

- **Compact, powerful cordless drill with forward/reverse operation.**
- **Long service life thanks to brushless EC motor (not 070243).**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

KickBack control with auto power off in case of blockage and unique precision coupling and motor brake. 13mm auto-lock metal drill chuck. High torque.

With **wireless charging system**: automatic charging with special, battery-saving **induction charging technology**. Can be retrofitted with a **connectivity** module.

Supplied with:

Supplied with 2 Li-ion batteries, charger, transport case, belt clip, bit holder.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073851 ff. and 073866 ff for suitable spare batteries, starter sets and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Interface: wireless charging

Manufacturer's designation: GSR 18 V-60C

Motor design: Brushless motor

Battery voltage: 18 V

Battery capacity: 2 A·h

maximum torque soft: 31 N·m

maximum torque hard: 60 N·m

Technical description

maximum vibration to EN	<2.5 m/s ²
Quick-clamping chuck range	1.5 - 13 mm
Manufacturer's designation	GSR 18 V-60C
Weight	1.7 kg
Speed range 1st speed	0 - 600 rpm
typical application	Heavy Duty
suitable battery - supplier / battery type / voltage	Bosch 18 V
Speed range 2nd speed	0 - 1900 rpm
Packaging	Modular case (L-Boxx)
maximum torque hard	60 N·m
Interface	wireless charging
Motor design	Brushless motor
maximum twist drill size Ø in wood	38 mm
maximum twist drill size Ø in steel	13 mm
Battery capacity	2 A·h
Battery voltage	18 V
maximum torque soft	31 N·m

Accessories

Li-ion battery Battery type, battery voltage B18-W V	073851 B18-W
--	--------------

Wireless charging starter set Manufacturer's designation
GAL1830W

073862 GAL1830W