

Garant GRIDLINE

Perforated panel double-sided for ToolTruck, Usable height: 222mm**Order data**

Order number	914856 222
GTIN	4045197894021
Item class	9GT

Description**Version:**

Pair of support columns of 25×25 mm steel hollow section with sheet metal perforated panel (□ 9×9 mm on a 37-mm grid), silver powder-coated.

Perforated panel with grid.

Suitable for:

No. 914560, 914564, 914568.

Supplied with:

Sheet metal perforated panel with a pair of support columns.

Technical description

Perforated panel height	222 mm
Perforated panel width	1025 mm
Height	222 mm
Series	ToolTruck
Application range	Mobile workbench
Hoffmann perforated panel grid interval	9×9 mm
Type of product	Perforated rear panel