



Lace-up boot, black/blue VD PRO 1800 ESD, S2 NB BOA, EU shoe size: 40



Order data

| | |
|--------------|---------------|
| Order number | 092544 40 |
| GTIN | 4044348550717 |
| Item class | 09C |

Description

Version:

VARIO DYNAMICS® PRO range of safety shoes. VARIO Multiflex® technology for less shoe weight.

- **Upper made of a very light microfibre.**
- **Breathable functional lining.**
- **TPU Athletic ESD outer sole, light blue.**
- **Real leather insole.**
- **ERGO-SOFT ESD comfort mid-sole inlay.**
- **Protection against electrostatic discharge (ESD).**

Lace-up boots with seamless construction. Dust tongue. Padded trim.

With **SECURA VARIO® heel shock absorption.**

With BOA® rotary catch.

Standard:

EN ISO 20345:2011 S2 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Wide version XB, see No. 092545.

Stock goods in the EU shoe sizes 39 – 46. Can be ordered in the EU shoe sizes 36 – 50.

electrostatic characteristic: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Cold insulation: down to -20°C

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Drejelukning

Characteristics: Vario® damping

Technical description

| | |
|--------------------------------|--|
| Colour | black / blue |
| Protection class | S2 |
| EU shoe size | 40 |
| Cold insulation | down to -20°C |
| Material of protective toe-cap | Aluminium |
| Standard | Inlay type-tested according to DGUV regulation 191 |
| Series | VD PRO 1000 ESD |
| Characteristics | Drejelukning |
| Characteristics | Vario® damping |
| Gender | Gentlemen's |
| electrostatic characteristic | EGB/ESD |
| Type of product | Safety boots |