



Lace-up boot, black/blue VD PRO 1800 ESD, S2 NB BOA, EU shoe size: 39



Order data

Order number	092544 39
GTIN	4044348550700
Item class	09C

Description

Version:

VARIO DYNAMICS® PRO range of safety shoes. VARIO Multiflex® technology for less shoe weight.

- **Upper made of a very light microfibre.**
- **Breathable functional lining.**
- **TPU Athletic ESD outer sole, light blue.**
- **Real leather insole.**
- **ERGO-SOFT ESD comfort mid-sole inlay.**
- **Protection against electrostatic discharge (ESD).**

Lace-up boots with seamless construction. Dust tongue. Padded trim.

With **SECURA VARIO® heel shock absorption.**

With BOA® rotary catch.

Standard:

EN ISO 20345:2011 S2 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Wide version XB, see No. 092545.

Stock goods in the EU shoe sizes 39 – 46. Can be ordered in the EU shoe sizes 36 – 50.

electrostatic characteristic: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Cold insulation: down to -20°C

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Drejelukning

Characteristics: Vario® damping

Technical description

Protection class	S2
Standard	Inlay type-tested according to DGUV regulation 191
EU shoe size	39
Material of protective toe-cap	Aluminium
Cold insulation	down to -20°C
Colour	black / blue
Series	VD PRO 1000 ESD
Characteristics	Drejelukning
Characteristics	Vario® damping
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots