



Lace-up boot, black/blue VD PRO 1800 ESD, S2 XB BOA, EU shoe size: 40



Order data

Order number	092545 40
GTIN	4044348550953
Item class	09C

Description

Version:

VARIO DYNAMICS® PRO range of safety shoes. VARIO Multiflex® technology for less shoe weight.

- **Upper made of a very light microfibre.**
- **Breathable functional lining.**
- **TPU Athletic ESD outer sole.**
- **Real leather insole.**
- **ERGO-SOFT ESD comfort mid-sole inlay.**
- **Protection against electrostatic discharge (ESD).**

Lace-up boots of seam-free construction. Dust flap. Padded edges.

With BOA® rotary catch.

With **SECURA VARIO® heel shock absorption.**

Standard:

EN ISO 20345:2011 S2 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

EU shoe sizes 39 – 46 held in stock. EU shoe sizes 36 – 50 can be ordered.

electrostatic characteristic: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Drejelukning

Characteristics: Vario® damping

Technical description

EU shoe size	40
Material of protective toe-cap	Aluminium
Protection class	S2
Standard	Inlay type-tested according to DGUV regulation 191
Colour	black / blue
Series	VD PRO 1000 ESD
Characteristics	Drejelukning
Characteristics	Vario® damping
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots