

Garant GRIDLINE

**LED lamp for ToolTruck supplied with support columns, Type: 20****Order data**

Order number	914873 20
GTIN	4045197893765
Item class	9GT

**Description****Version:**

Lighting unit complete with lampholder and connecting cable and support arms for mounting on support columns of roller cabinets and mobile workbenches. A carrier arm with break-through for leading the cable through the support columns. Maintenance-free LED technology with long working life. The energy-efficient light source is exceptionally uniform, dazzle-free and flicker-free, with a neutral white light and a light temperature of 4000 K.

The lamp incorporates built-in LED bulbs. The bulbs cannot be replaced within the lamp.

**Suitable for:**

No. 914560, 914564, 914568, 914574, 914575.

**Supplied with:**

LED light including power supply unit, with Wieland plug for connection to cable reels, 2 support arms.

**Note:**

Also order cable roll-up drum no. 914890 size DE for the power connection.

**Technical description**

Lamp body height	33 mm
Illumination	2800 lm

Lamp body length	1030 mm
Power supply	Mains-powered
Lamp body width	123 mm
Power consumption	35 W
Support arm reach	350 mm
Series	ToolTruck
ATEX zone	no
Nominal voltage	250 V
Plug type, input	GST plug-in system
Type of product	Mounted light

---

## Accessories

LED lamp for ToolTruckwithout support columns Type 20	914872 20
---	-----------