



Double-ended open ring spanner, Width across flats: 10X11 mm



Order data

Order number	619705 10X11
GTIN	4045197673343
Item class	62A

Description

Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

Standard:

DIN 3118 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum ring $\varnothing D_2$ max	21.4 mm
Width across flats 1	10 mm
maximum ring $\varnothing D_1$ max	19.4 mm
Width across flats 2	11 mm
maximum ring height $h_{2\max}$	8.5 mm
Spanner length L	153 mm
maximum ring height $h_{1\max}$	8 mm
Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10 degrees

Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner