



## Double-ended open ring spanner, Width across flats: 12X14 mm



### Order data

Order number	619200 12X14
GTIN	4018754021932
Item class	63A

### Description

#### Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With easy-grip fluted shaft. Optimum flexural strength, good torque transmission, very light and easy to use. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

#### Standard:

**DIN 3118 / ISO 3318**

#### Material:

Chrome alloy steel; non-flaking, chrome-plated over nickel.

Spanner length L: 180 mm

maximum ring  $\varnothing D_1$  max: 24 mm

maximum ring  $\varnothing D_2$  max: 26 mm

maximum ring height  $h_{1\max}$ : 9.5 mm

maximum ring height  $h_{2\max}$ : 10.5 mm

### Technical description

Spanner length L	180 mm
maximum ring height $h_{1\max}$	9.5 mm
maximum ring $\varnothing D_2$ max	26 mm
maximum ring $\varnothing D_1$ max	24 mm
Width across flats 2	14 mm
Width across flats 1	12 mm

maximum ring height $h_{2\max}$	10.5 mm
Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10 °
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated (non-flaking)
open ring	yes
Type of product	Spanner