

**Endoscope probe, elbow bend, flexible, 4.5 mm Ø, Probe length: 1500mm****Order data**

Order number	492944 1500
GTIN	4045197893772
Item class	42L

**Description****Version:**

**2x 180° flexible probe head:** Probe with hand grip and setting handle for bending the camera head in two directions (maximum 2x 180°). For inspection of voids opposite the direction of entry of the probe, no additional probe mirror is needed. A stop function for the desired angular position allows non-fatiguing working. Complete probe with metal-braided protective hose, particularly resistant. Image aperture angle 90°.

Sturdy watertight probe head (IP67) of stainless steel with dimmable white LEDs. Direction of view 0°.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

Ideal for inspection of voids where access is difficult, e.g. **automotive:** Engine, gearbox, fuel tank, bodywork, dashboard, appraisal. **Aerospace:** engines, turbines, pipework, and wiring systems. **Buildings:** Assessment of the structure of buildings, water damage, pest infestation.

**Pipework systems:** weld seams, traces of foreign bodies, leaks. **Hydraulic systems:** cylinders, leaks. **Heating - sanitation - air conditioning:** ovens, furnaces, boilers, air conditioning systems, drainage systems. **Pest control:** Bees' nests, wasps' nests, birds' nests, insect entry points. **Police, customs:** Vehicle checking, goods checking.

**Suitable for:**

All endoscope versions No. 492923; 492924; 492925; 492928.

**Note:**

Other types of probe (up to 30 m) with other probe head  $\varnothing$  and directions of view available on request.

---

## Technical description

IP Index of Protection	IP 67
Camera resolution	640×480 px
Product name attribute	4.5 mm $\varnothing$
Type of product	Probe