



Lace-up boot, anthracite STAVANGER Bau GORE II, S3 NB, EU shoe size: 47



Order data

Order number	092781 47
GTIN	4044348293720
Item class	09C

Description

Version:

STAVANGER Bau GORE II lace-up boots with GORE-TEX® membrane for a breathable but still waterproof upper material made of supple waterproof leather. Good resistance to acids and alkalis. High level of cutting resistance and mechanical strength. Wide tread. Extremely anti-slip, even on smooth, wet and oily floors. With **SECURA VARIO® heel shock absorption** and heat-resistance up to approx. 220°C.

- **Closed tongue.**
- **Perbunan Alpine sole, anthracite.**
- **Reinforced toe protection.**
- **Lace hooks.**
- **Elevated shank.**
- **Padded edges.**
- **Real leather insole.**
- **ERGO-COOL® comfort mid-sole inlay.**

Version of the advertising text:

STAVANGER Bau GORE II lace-up boots with GORE-TEX® membrane for a breathable but still waterproof upper material made of supple waterproof leather. Good resistance to acids and alkalis. High level of cutting resistance and mechanical strength. Wide tread. Extremely anti-slip, even on smooth, wet and oily floors. Withstands heat up to approx. 220 °C.

- **Closed tongue.**
- **Perbunan Alpine sole, anthracite.**
- **Reinforced toe protection.**
- **Lace hooks.**
- **Longer boot leg.**
- **Padded edges.**
- **Real leather insole.**
- **ERGO-COOL® comfort mid-sole inlay.**

Standard:

EN ISO 20345:2011 S3 SRC CI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Stock goods in the EU shoe sizes 39 – 46, can be ordered in the EU shoe sizes 36 – 51.

Wide version XB, see No. 092782. Includes the damping element red and black

Note re advertising text:

Wide version XB, see No. 092782.

Technical description

Protection class	S3
Puncture resistance	Steel
Standard	Inlay type-tested according to DGUV regulation 191
EU shoe size	47
Cold insulation	down to -20°C
Material of protective toe-cap	Steel
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Characteristics	Vario® damping
Gender	Gentlemen's
Type of product	Safety boots