



## Double-ended open ring spanner, Width across flats: 12X14 mm



### Order data

Order number	619705 12X14
GTIN	4045197673374
Item class	62A

### Description

#### Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

#### Standard:

**DIN 3118 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 174 mm

maximum ring  $\varnothing D_1$  max: 22.8 mm

maximum ring  $\varnothing D_2$  max: 25.3 mm

maximum ring height  $h_{1\max}$ : 8.5 mm

maximum ring height  $h_{2\max}$ : 10.5 mm

### Technical description

maximum ring $\varnothing D_1$ max	22.8 mm
Width across flats 1	12 mm
maximum ring height $h_{2\max}$	10.5 mm
Width across flats 2	14 mm
Spanner length L	174 mm
maximum ring $\varnothing D_2$ max	25.3 mm
maximum ring height $h_{1\max}$	8.5 mm

Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10°
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner