



Double ended ring spanner, straight, for Torx® screws, Torx® profile: E10XE12



Order data

Order number	619400 E10XE12
GTIN	4018754022359
Item class	63A

Description

Version:

Drop forged, straight design. Flat heads and thin rings for restricted places. Fluted shaft.

Material:

Chrome alloy steel, chrome-plated over nickel.

Spanner length L: 149.5 mm

maximum ring $\varnothing D_1$ max: 13.7 mm

maximum ring $\varnothing D_2$ max: 15.7 mm

maximum ring height $h_{1\max}$: 6.5 mm

maximum ring height $h_{2\max}$: 7.5 mm

Technical description

Torx® profile 2	E12
maximum ring $\varnothing D_1$ max	13.7 mm
maximum ring height $h_{2\max}$	7.5 mm
Spanner length L	149.5 mm
maximum ring $\varnothing D_2$ max	15.7 mm
maximum ring height $h_{1\max}$	6.5 mm
Torx® profile 1	E10
Manufacturing process	drop forged
Material	Chrome alloy steel
Type of product	Spanner

